



WPS51B

## 1G 5A Unswitched Socket & Back Box without Knockouts

### Technical Features

#### Electric current

Rated current	5 A
---------------	-----

#### Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	Grey
Surface finish	Matt
Material	Steel
Treatment	Epoxy

#### Dimensions

Height	86 mm
Width	86 mm
Depth	53.20 mm

#### Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

#### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

#### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	Yes
With signal lamp	No

#### Accessories

Has labelling field	No
---------------------	----

#### Capacity

Number of modules	0
-------------------	---

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Functions

With orientation lighting	No
With function lighting	No

#### Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With earth connection
Protection	Enhanced contact protection

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes