



67303909

Change-over switch, 2-pole 10 AX, light control

Technical Features

Electric current

Switching current	10 A
-------------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Material	Metal Plastic
----------	------------------

Identification

Assembly arrangement	Basic element
----------------------	---------------

Connectivity

Mounting type	Clamp mounting Screw connection
---------------	------------------------------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	71 x 71 mm
Built-in depth	31 mm
Built-in depth flush-mounted boxes	35 mm

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Electric current

Rated current	10 A
---------------	------

Texts

Type of connection	With screw terminals
Lighting	Can be illuminated with neon lamp unit For illumination
Switch mode	2-pole off/change-over