



2844

Technical Features

Architecture

Number of poles	2
-----------------	---

Voltage

Rated voltage	230 V
Type voltage supply	AC

Frequency

Frequency	50 - 60 Hz
-----------	------------

Electric current

Rated current	16 A
Breaking and opening capacity $I_{dm}$	3 kA
Rated residual operating current $I_{dn}$	30 mA

Safety

Residual current type	A
Ingress Protection (IP) class	IP20

Connection

Cross-section of input and output with screws, for massive conductors	1.5 - 2.5 mm <sup>2</sup>
---	---------------------------

Use conditions

Operating temperature	-25 - 40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2

Capacity

Number of modules	0
-------------------	---

Dimensions

Depth	45 mm
Built-in depth	32 mm

Texts

Installation mode	For flush-mounted and hollow wall mounting Without spreader claws
Protection	To protect downstream loads
Type	Type A for alternating currents and pulsating direct currents
Type of connection	With plug-in terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes