




EE815



Presence detector 360° monobloc, flush mounted, white

Technical Features

Detection

Detection angle	360 - 360
Type of sensor	Presence detector

Settings

Time delay	1 Min - 1 h
------------	-------------

Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Recommended installation height	2.5 - 3.5 m
---------------------------------	-------------

Use conditions

Operating temperature	-10 - 45 °C
-----------------------	-------------

Materials

Colour	White
Material	Plastic

Safety

Ingress Protection (IP) class	IP41
-------------------------------	------

Installation, mounting

Mounting on	Flush mounting
Suitable for outdoor usage	Yes

Texts

Function	Can only be used as individual unit
Installation mode	With spring clips for ceiling installation
Type of connection	With screw terminals

Sustainability

RoHS conform	Yes
--------------	-----