



WMGSDP2N/FF

**20A 1 Way Double Pole Switch with LED Indicator Marked 'FRIDGE FREEZER'**

**Technical Features**

**Electric current**

Switching current	20 A
-------------------	------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Voltage**

Rated voltage	250 V
---------------	-------

**Materials**

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Urea formaldehyde
----------	-------------------

Treatment	Untreated
-----------	-----------

**Identification**

Assembly arrangement	Basic element with central cover plate
----------------------	--

**Connectivity**

Mounting type	Snap-on mounting
---------------	------------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Dimensions	59 x 25 mm
------------	------------

Built-in depth	13.10 mm
----------------	----------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Architecture**

Control/operation element	Single rocker
---------------------------	---------------

**Electric current**

Rated current	20 A
---------------	------

**Texts**

Lighting	With control LED for ON
----------	-------------------------

Switch mode	2-pole
-------------	--------

**Sustainability**

RoHS conform	Yes
--------------	-----