



MMN201

Magnetic MCB 2P 25kA 1.25A 400V Zubehörmöglich. Anzeige IEC 947-2

Technical Features

Electric current

| | |
|-------------------------------------------------------------------------------|--------|
| Rated current | 1.25 A |
| Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2 | 20 kA |
| Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2 | 50 kA |
| Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2 | 25 kA |

Architecture

| | |
|--------------|-----|
| Type of pole | 2P |
| Curve | Mag |

Capacity

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Installation, mounting

| | |
|-----------------------------------------|----------------|
| Nominal tightening torque top terminal | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |

Voltage

| | |
|--------------------------------------|-------------|
| Rated operational voltage Ue | 415 - 415 V |
| Type voltage supply | AC |
| Rated insulation voltage Ui | 500 V |
| Rated impulse withstand voltage Uimp | 6000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Connection

| | |
|------------------------------------------------------------------------|------------------------|
| Cross-section of input and output with screws, for massive conductors | 1 - 35 mm ² |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for flexible conductors | 1 - 25 mm ² |
| Cross-section of input with screws, for massive conductors | 1 - 35 mm ² |

Installation, mounting

| | |
|-----------------------------------------------|----------------|
| Nominal tightening torque | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect |
| Type of top connection for modular devices | Screw terminal |
| 360° mounting position possible | Yes |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Use conditions

| | |
|----------------------------------------------------------|------------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
| Air humidity protection | For all climates |
| Operating temperature | -25 - 70 °C |

Power

| | |
|---------------------------|--------|
| Total power loss under IN | 1.50 W |
|---------------------------|--------|

Connectivity

| | |
|-----------------------------------------------|------------------|
| Type of connection | Screw terminal |
| Top connection alignment for modular devices | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |

Dimensions

| | |
|--------|-------|
| Height | 83 mm |
| Width | 35 mm |
| Depth | 70 mm |

Illustrations | Drawings

