



LFH6009009016

**Trunking halogen free LFH 60x90mm traffic white**

**Technical Features**

**Dimensions**

Height	60 mm
Width	90 mm
Length	2000 mm
Inner cross-section	4360 - 4360 mm <sup>2</sup>

**Capacity**

Max. number of cables (Ø11mm, 50% filled, without devices)	18
--	----

**Materials**

Material	PC-ABS
Treatment	Untreated
RAL code	9016
Colour	Traffic white

**Safety**

Impact resistance IK	IK07
Ingress Protection (IP) class	IP30

**Standards**

Suitable for functional integrity according to DIN4102-12	No
---	----

**Use conditions**

Operating temperature	-5 - 90 °C
-----------------------	------------

**Connectivity**

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

**Equipment**

Number of partitions	0
Number of compartments	1 - 1
Number of pluggable partitions	1
Cable retaining clip included	Yes
With protective film	No

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

**Illustrations | Drawings**

