



3315417009



**VGA soc. out., screw-in lift terminals, K.1, p. white glossy**

**Technical Features**

**Connection**

|                         |                             |
|-------------------------|-----------------------------|
| Connector/plug type     | VGA                         |
| Conductor cross-section | 1.50 - 1.50 mm <sup>2</sup> |
| Number of connections   | 1                           |

**Frequency**

|                 |         |
|-----------------|---------|
| Frequency video | 160 MHz |
|-----------------|---------|

**Materials**

|                |                  |
|----------------|------------------|
| Colour         | Polar white      |
| RAL code       | 9010             |
| Surface finish | Glossy           |
| Material       | Metal<br>Plastic |
| Treatment      | Untreated        |

**Dimensions**

|                                    |          |
|------------------------------------|----------|
| Height                             | 71 mm    |
| Width                              | 71 mm    |
| Depth                              | 23.50 mm |
| Built-in depth flush-mounted boxes | 13 mm    |

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

**Equipment**

|                 |     |
|-----------------|-----|
| Shielded        | Yes |
| With dust cover | No  |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Texts**

|                                  |                         |
|----------------------------------|-------------------------|
| Outlet                           | With straight outlet    |
| Labelling                        | Without labelling field |
| Supporting plate/supporting ring | With supporting ring    |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |