



TXM632C



OUTPUT DEVICE FOR 12 SHUTTERS / BLINDS 230V~ 4A / NE

Technical Features

Settings

| | |
|------------------------------|-------------|
| Supported configuration mode | ETS easy |
|------------------------------|-------------|

Connectivity

| | |
|---------------------------|----|
| With bus system KNX radio | No |
|---------------------------|----|

Installation, mounting

| | |
|-------------|----------|
| Mounting on | DIN rail |
|-------------|----------|

Materials

| | |
|--------|------------|
| Colour | Light grey |
|--------|------------|

Equipment

| | |
|-------------------------------|-----|
| With switch for manual switch | Yes |
|-------------------------------|-----|

Electric current

| | |
|------------------------|-----|
| Rated current | 4 A |
| Max. switching current | 4 A |

Voltage

| | |
|----------------------------|-----------|
| Operating voltage over bus | 21 - 32 V |
|----------------------------|-----------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Connection

| | |
|----------------------------------|-------------------------|
| Cross-section flexible conductor | 0.5 - 6 mm ² |
| Cross-section rigid conductor | 0.5 - 6 mm ² |

Capacity

| | |
|-------------------|----|
| Number of modules | 10 |
|-------------------|----|

Texts

| | |
|--------------------|---|
| Function | With safety functions e.g. for wind, rain, alarm With positioning function for blind and lamella position With sun shade function |
| Type of connection | With screw terminals |
| Operating mode | Operating mode can be set for roller shutter/awning |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|