



VE110SN

Enclosure,vector,flush mounted,IP65,10M,UV-stable,without cable entry

### Technical Features

#### Voltage

Nominal voltage	400 - 400 V
Rated operational voltage in DC	1000 - 1000 V

#### Installation, mounting

Suitable for outdoor usage	Yes
Mounting on	Surface mounting

#### Electric current

Rated current	63 A
---------------	------

#### Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

#### Capacity

Number of modules	10
-------------------	----

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	210 mm
Width	237 mm
Depth	114 mm

#### Cover, door

Number of cabinet doors	1
Number of locks	0

#### Dimensions

Number of width units	10
-----------------------	----

#### Cover, door

Door/cover is transparent	Yes
---------------------------	-----

#### Connection

Number of conduit inlets	6
--------------------------	---

#### Materials

Material	Polycarbonate (PC)
RAL code	7035
Colour	Light grey

#### Equipment

Has earthing terminal block	No
Has mounting plate	No

#### Materials

Ultraviolet-resistant	Yes
-----------------------	-----

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP65
Locking type	Snap on lock Without lock
Glow wire test	850 °C

Product Datasheet  
VE110SN

Sustainability	
RoHS conform	Yes