




TYA661BN



**Dimmer 1 channel 600W**

**Technical Features**

**Voltage**

|                            |                 |
|----------------------------|-----------------|
| Operating voltage over bus | 21 - 32 V       |
| Input voltage              | 230 - 230 V     |
| System supply voltage      | 30 V DC Via bus |
| Auxiliary tension          | 230 - 230 V     |

**Electric current**

|                                       |         |
|---------------------------------------|---------|
| Bus current consumption data transfer | 2.30 mA |
|---------------------------------------|---------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

**Connection**

|                                  |                            |
|----------------------------------|----------------------------|
| Cross-section flexible conductor | 0.75 - 2.5 mm <sup>2</sup> |
| Cross-section rigid conductor    | 0.75 - 2.5 mm <sup>2</sup> |

**Equipment**

|                   |   |
|-------------------|---|
| Number of outputs | 1 |
|-------------------|---|

**Lighting**

|                |       |
|----------------|-------|
| LED lamp power | 120 W |
|----------------|-------|

**Equipment**

|                |                  |
|----------------|------------------|
| Type of dimmer | Dimming actuator |
|----------------|------------------|

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

**Power**

|                                     |             |
|-------------------------------------|-------------|
| 230 V incandescent and halogen lamp | 600 W       |
| Power incandescent lamp             | 600 - 600 W |
| Power of variator                   | 600 - 600 W |

**Connectivity**

|                           |              |
|---------------------------|--------------|
| With bus system KNX radio | No           |
| Type of connection        | quickconnect |

**Lighting**

|                         |             |
|-------------------------|-------------|
| Dimmable 230 V LED lamp | 120 - 120 W |
|-------------------------|-------------|

**Settings**

|                              |     |
|------------------------------|-----|
| Supported configuration mode | ETS |
|------------------------------|-----|

**Texts**

|                    |  |
|--------------------|--|
| Fuse               | Overheating protection (display using LEDs)<br>Short-circuit proof and overload-proof (display using LEDs)                     |
| Dimming principle  | Phase cut-on or cut-off according to load type, self-learning<br>Minimum/maximum dimming values per channel settable on device |
| Function           | Learning function for optimised operation of compact fluorescent<br>lamps and LED luminaires can be activated via the bus      |
| Type of connection | With quickconnect plug-in terminals  |
| Labelling          | Large labelling field  |
| Protection         | With overheating, overload and short-circuit protection  |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|