



WGDL122NB

**16AX 2G 2W switch;nb**

**Technical Features**

**Electric current**

Switching current 16 A

**Voltage**

Rated voltage 250 V

**Materials**

Colour Bronze

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

**Controls and indicators**

Number of buttons 2

**Dimensions**

Dimensions 86 x 86 mm

Built-in depth flush-mounted boxes 35 mm

**Safety**

Ingress Protection (IP) class IP20

**Architecture**

Control/operation element Double rocker

**Electric current**

Rated current 16 A

**Texts**

Switch mode 2-way

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes