



CR64AXILSF2.0

CR64AX c/w 4 Core 0.75mm² 2m LSOH Lead

Technical Features

Architecture

| | |
|-----------------|---|
| Number of poles | 4 |
|-----------------|---|

Voltage

| | |
|------------------------|-------|
| Max. operating voltage | 240 V |
|------------------------|-------|

Electric current

| | |
|---------------|-----|
| Rated current | 6 A |
|---------------|-----|

Cable

| | |
|----------------|------|
| Cable diameter | 7 mm |
|----------------|------|

| | |
|--------------|-----|
| Cable length | 2 m |
|--------------|-----|

Dimensions

| | |
|--------|---------|
| Length | 2000 mm |
|--------|---------|

Connection

| | |
|-------------------------|-----------------------------|
| Conductor cross-section | 0.75 - 0.75 mm ² |
|-------------------------|-----------------------------|

Equipment

| | |
|-------------------|-----|
| Mechanical coding | Yes |
|-------------------|-----|

| | |
|-------------------|------|
| Type cable side 1 | Plug |
|-------------------|------|

| | |
|-------------------|--------------------|
| Type cable side 2 | Free conductor end |
|-------------------|--------------------|

| | |
|---------------|-------------------------|
| Type of cable | Device connection cable |
|---------------|-------------------------|

Use conditions

| | |
|--|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
|--|---|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

Cable

| | |
|--|-------|
| Cable permanent temperature resistant to | 90 °C |
|--|-------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|