



EGN103



**1 channel digital time switch weekly cycle**

**Technical Features**

**Voltage**

Nominal voltage	230 - 230 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power**

230 V incandescent and halogen lamp	2300 W
-------------------------------------	--------

**Lighting**

Max. load fluorescent lamp in series	1000 W
Max. load fluorescent lamp parallel compensated	400 VA

**Functions**

Power reserve in years	5 y
With network synchronisation	No
With quartz synchronisation	Yes
Number of function channels	1

**Equipment**

Accuracy per day	1.50 s
With impulse programme	No
Number of channels	1

**Connection**

Type of contacts	1x changeover
------------------	---------------

**Settings**

Daily programme	Yes
Weekly programme	Yes
Annual programme	No

**Use conditions**

Operating temperature	-5 - +45 °C
-----------------------	-------------

**Connection**

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>

**Texts**

Type of connection	With screw terminal
--------------------	---------------------

**Dimensions**

Height	85 mm
Width	35.80 mm
Depth	61.60 mm

**Main electrical attributes**

Minimum interval between 2 switching times	1 min
--	-------

**Capacity**

Number of modules	2
-------------------	---

**Sustainability**

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

