



ADC932R

**Bidirectional RCBO 1M 1P+N 6kA C-32A 30mA type A**

**Technical Features**

**Architecture**

Type of pole	1P+N
Curve	C

**Electric current**

Rated current	32 A
Rated residual operating current I <sub>dn</sub>	30 mA
Rated current -25°C	38.60 A
Rated current at -20°C	38 A
Rated current -15°C	37.40 A
Rated current -10°C	36.80 A
Rated current -5°C	36.20 A
Rated current at 0°C	35.60 A
Rated current 5°C	35 A
Rated current 10°C	34.40 A
Rated current 15°C	33.80 A
Rated current at 20°C	33.20 A
Rated current 25°C	32.60 A
Rated current 30°C	32 A
Rated current 35°C	31.30 A
Rated current at 40°C	30.70 A
Rated current at 50°C	29.30 A
Rated current 55°C	28.60 A
Rated current 60°C	28 A
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP20

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

**Voltage**

Rated insulation voltage U <sub>i</sub>	440 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Max. operating voltage	264 V
Rated operational voltage U <sub>e</sub>	230 - 230 V
Overvoltage category according to IEC 60947-1	3

**Power**

Total power loss under I <sub>N</sub>	12.48 W
---------------------------------------	---------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Use conditions**

Max. Altitude	2000 m
Class of energy limitation I <sup>2</sup> t	3

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Connection**

Cross-section of input with screws, for flexible conductors	1 - 10 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 16 mm <sup>2</sup>

---

**Capacity**

Number of modules	1
-------------------	---

---

**Installation, mounting**

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

---

**Dimensions**

Height	85 mm
Width	17.70 mm
Depth	70 mm

---

**Use conditions**

Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C

---

**Connection**

Cross-section of input and output with screws, for flexible conductors	1 - 10 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1 - 16 mm <sup>2</sup>

---

**Compatibility**

Suitable for DIN Rail	Yes
-----------------------	-----

---

**Sustainability**

RoHS conform	Yes
--------------	-----