



ADC916R

**Bidirectional RCBO 1M 1P+N 6kA C-16A 30mA type A**

**Technical Features**

**Architecture**

Type of pole	1P+N
Curve	C

**Electric current**

Rated current	16 A
Rated residual operating current Idn	30 mA
Rated current -25°C	20.50 A
Rated current at -20°C	20.10 A
Rated current -15°C	19.70 A
Rated current -10°C	19.30 A
Rated current -5°C	18.90 A
Rated current at 0°C	18.50 A
Rated current 5°C	18.10 A
Rated current 10°C	17.60 A
Rated current 15°C	17.20 A
Rated current at 20°C	16.80 A
Rated current 25°C	16.40 A
Rated current 30°C	16 A
Rated current 35°C	15.70 A
Rated current at 40°C	15.50 A
Rated current at 50°C	15 A
Rated current 55°C	14.70 A
Rated current 60°C	14.50 A
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP20

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

**Voltage**

Rated insulation voltage Ui	440 V
Rated impulse withstand voltage Uimp	4000 V
Max. operating voltage	264 V
Rated operational voltage Ue	230 - 230 V
Oversupply category according to IEC 60947-1	3

**Power**

Total power loss under IN	8.69 W
---------------------------	--------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Use conditions**

Max. Altitude	2000 m
Class of energy limitation I <sup>2</sup> t	3

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Connection**

Cross-section of input with screws, for flexible conductors	1 - 10 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 16 mm <sup>2</sup>

<b>Capacity</b>	
Number of modules	1
<b>Installation, mounting</b>	
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect
<b>Dimensions</b>	
Height	85 mm
Width	17.70 mm
Depth	70 mm
<b>Use conditions</b>	
Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C
<b>Connection</b>	
Cross-section of input and output with screws, for flexible conductors	1 - 10 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1 - 16 mm <sup>2</sup>
<b>Compatibility</b>	
Suitable for DIN Rail	Yes
<b>Sustainability</b>	
RoHS conform	Yes