



SPB065N

**Cartridge N-PE Uc 260V In 20kA I<sub>max</sub> 65kA Up 1,5kV**

**Technical Features**

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

**Voltage**

|                                                                             |             |
|-----------------------------------------------------------------------------|-------------|
| Rated operational voltage U <sub>e</sub>                                    | 240 - 415 V |
| Continuous operating voltage U <sub>c</sub> according to IEC 61643-1        | 264 V       |
| Voltage protection level U <sub>p</sub> L-PE/N-PE according to IEC 61643-11 | 1.7 kV      |

**Electric current**

|                                                                            |       |
|----------------------------------------------------------------------------|-------|
| Nominal discharge current I <sub>n</sub> 8 - 20 μs L-N(PEN)/N-PE IEC 61643 | 50 kA |
|----------------------------------------------------------------------------|-------|

**Dimensions**

|        |         |
|--------|---------|
| Height | 47.3 mm |
| Width  | 17.5 mm |
| Depth  | 67.3 mm |

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -40 - 80 °C |
|-----------------------|-------------|

**Network configuration**

|              |            |
|--------------|------------|
| Network type | TN-S<br>TT |
|--------------|------------|

**Connection**

|                                                                        |                            |
|------------------------------------------------------------------------|----------------------------|
| Cross-section of input and output with screws, for flexible conductors | 1.5 - 25.0 mm <sup>2</sup> |
| Cross-section of input and output with screws, for massive conductors  | 1.5 - 35.0 mm <sup>2</sup> |

**Standards**

|                             |          |
|-----------------------------|----------|
| Requirement class IEC 61643 | T1<br>T2 |
|-----------------------------|----------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Installation, mounting**

|                           |          |
|---------------------------|----------|
| Nominal tightening torque | 3 - 3 Nm |
|---------------------------|----------|

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |