



LS601

Fuse carrier 1P 50A 690V L51 accessoriability 1.5M

Technical Features

Dimensions

Height	107 mm
Width	26.25 mm
Depth	93 mm

Architecture

Number of poles	1
-----------------	---

Electric current

Rated current	50 A
Rated current of fuse cartridge	2 A
	4 A
	6 A
	8 A
	10 A
	12 A
	16 A
	20 A
	25 A
	32 A
	40 A
	50 A

Capacity

Number of modules	1.50
-------------------	------

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Installation, mounting

Nominal tightening torque	3.5- 3.5 Nm
Mounting on	DIN rail

Power

Total power loss under IN	6.09 W
---------------------------	--------

Voltage

Rated insulation voltage Ui	690 V
Rated impulse withstand voltage Uimp	8 kV
Type voltage supply	AC
Overvoltage category according to IEC 60947-1	3

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Cross-section of input and output with screws, for flexible conductors	16 - 16 mm ²
Cross-section of input and output with screws, for massive conductors	25 - 25 mm ²

Fuse

Fuse size	14 x 51
-----------	---------

Cover, door

Interlockable	Yes
---------------	-----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

