



LS604

**Fuse carrier 3P+N 50A 690V L51 accessoriability 6M**

**Technical Features**

**Dimensions**

Height	107 mm
Width	105 mm
Depth	93 mm

**Architecture**

Number of poles	4
-----------------	---

**Electric current**

Rated current	50 A
Rated current of fuse cartridge	2 A
	4 A
	6 A
	8 A
	10 A
	12 A
	16 A
	20 A
	25 A
	32 A
	40 A
	50 A

**Capacity**

Number of modules	6
-------------------	---

**Use conditions**

Operating temperature	-5 - 40 °C
-----------------------	------------

**Installation, mounting**

Nominal tightening torque	3.5 -3.5 Nm
Mounting on	DIN rail

**Power**

Total power loss under IN	20.16 W
---------------------------	---------

**Voltage**

Rated insulation voltage Ui	690 V
Rated impulse withstand voltage Uimp	8 kV
Type voltage supply	AC
Overvoltage category according to IEC 60947-1	3

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Connection**

Cross-section of input and output with screws, for flexible conductors	16 - 16 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	25 - 25 mm <sup>2</sup>

**Fuse**

Fuse size	14 x 51
-----------	---------

**Cover, door**

Interlockable	Yes
---------------	-----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

