



LS612

Fuse carrier 1P+N 50A 690V L51 accessoriability 3M

Technical Features

Dimensions

Height	107 mm
Width	52.50 mm
Depth	93 mm

Architecture

Number of poles	2
Type of pole	1P+N

Electric current

Rated current	50 A
Rated current of fuse cartridge	2 A 4 A 6 A 10 A 12 A 16 A 20 A 25 A 32 A 40 A 50 A

Capacity

Number of modules	3
-------------------	---

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Installation, mounting

Nominal tightening torque	3.5 - 3.5 Nm
Mounting on	DIN rail

Power

Total power loss under IN	8.30 W
---------------------------	--------

Voltage

Rated insulation voltage U_i	690 V
Rated impulse withstand voltage U_{imp}	8 kV
Type voltage supply	AC
Overvoltage category according to IEC 60947-1	3

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Cross-section of input and output with screws, for flexible conductors	16 - 16 mm ²
Cross-section of input and output with screws, for massive conductors	25 - 25 mm ²

Fuse

Fuse size	14 x 51
-----------	---------

Cover, door

Interlockable	Yes
---------------	-----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

