
Product Datasheet
HHA078Z



HHA078Z

Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 80A 25kA CTC

Technical Features

Electric current	
Rated current IN	80 A
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	25 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	20 kA
Rated current at 10°C according to IEC 60947	106.90 A
Rated current at 15°C according to IEC 60947	103.90 A
Rated current at 20°C according to IEC 60947	100.90 A
Rated current at 25°C according to IEC 60947	97.70 A
Rated current at 30°C according to IEC 60947	94.40 A
Rated current at 35°C according to IEC 60947	91 A
Rated current at 40°C according to IEC 60947	87.50 A
Rated current at 45°C according to IEC 60947	83.80 A
Rated current at 50°C according to IEC 60947	80 A
Rated current at 55°C according to IEC 60947	75.90 A
Rated current at 60°C according to IEC 60947	71.60 A
Rated current at 65°C according to IEC 60947	67.10 A
Rated current at 70°C according to IEC 60947	62.20 A
Architecture	
Number of poles	1
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral
Tripping	
Response time when opening	10 ms
Frequency	
Frequency	50 - 60 Hz
Voltage	
Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	690 V
Rated operational voltage Ue	220 - 240 V
Functions	
Trip unit	TM F/F
Power	
Power dissipation at IN	4.80 W
Endurance	
Electric endurance in number of cycles	10000
Number of mechanical operations	20000
Safety	
Ingress Protection (IP) class	IP4X
Connection	
Cross-section flexible conductor	4 - 70 mm^2
Cross-section rigid conductor	4 - 95 mm^2
Installation, mounting	
Mounting-/Connection Position	Front
Connectivity	
Type of connection	Screw terminal

Settings	
Thermal protection knob setting xIN	1 1

Dimensions	
Height	130 mm
Width	25 mm
Depth	68 mm

Compatibility	
Suitable for DIN Rail	Yes

Main electrical attributes	
Magnetic protection trip time	0 - 0 ms

Sustainability	
REACh-SVHC free	Yes
RoHS conform	Yes