



LF408M

Industrial fuse-links 14x51 aM 8A

Technical Features

Fuse

|                      |         |
|----------------------|---------|
| Fuse characteristics | aM      |
| Fuse size            | 14 x 51 |

Electric current

|               |     |
|---------------|-----|
| Rated current | 8 A |
|---------------|-----|

Power

|                                       |        |
|---------------------------------------|--------|
| Total power loss under I <sub>N</sub> | 0.70 W |
|---------------------------------------|--------|

Main electrical attributes

|                                                                                   |       |
|-----------------------------------------------------------------------------------|-------|
| Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1 | 80 kA |
|-----------------------------------------------------------------------------------|-------|

Voltage

|                     |             |
|---------------------|-------------|
| Type voltage supply | AC          |
| Nominal voltage     | 690 - 690 V |

Architecture

|       |   |
|-------|---|
| Curve | C |
|-------|---|

Sustainability

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |