



SPB408D

**Surge Protection Device 4P TNS/TT U<sub>c</sub> 275V I<sub>n</sub> 2 kA I<sub>max</sub> 8 kA U<sub>p</sub> 1kV**

**Technical Features**

**Capacity**

Number of modules	4
-------------------	---

**Voltage**

Rated operational voltage U <sub>e</sub>	240 - 415 V
Continuous operating voltage U <sub>c</sub> according to IEC 61643-1	275 V
Voltage protection level U <sub>p</sub> according to IEC 61643-1	0.90 kV
Voltage protection level U <sub>p</sub> L-PE/N-PE according to IEC 61643-11	1.50 kV
Voltage level U <sub>p</sub> L-N/PEN IEC 61643-11	900 V

**Electric current**

Nominal discharge current I <sub>n</sub> 8 - 20 μs L-N(PEN)/N-PE IEC 61643	2 kA 20 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	8 kA 40 kA

**Dimensions**

Height	89.80 mm
Width	71 mm
Depth	65.7 mm

**Use conditions**

Operating temperature	-40 - 80 °C
-----------------------	-------------

**Network configuration**

Network type	TN-S TT
--------------	------------

**Equipment**

With remote signalling contact	No
--------------------------------	----

**Connection**

Cross-section of input and output with screws, for flexible conductors	1.5 - 25.0 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1.5 - 35.0 mm <sup>2</sup>

**Standards**

Requirement class IEC 61643	T2
-----------------------------	----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Installation, mounting**

Nominal tightening torque	3 - 4.5 Nm
---------------------------	------------

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes