



LF316M

Cylindrical fuse-links for industrial applications 10x38mm aM 16A 500V AC 120kA

**Technical Features**

**Fuse**

|                      |           |
|----------------------|-----------|
| Fuse characteristics | aM        |
| Fuse size            | 10.3 x 38 |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

**Power**

|                           |        |
|---------------------------|--------|
| Total power loss under IN | 0.92 W |
|---------------------------|--------|

**Main electrical attributes**

|   |        |
|---|--------|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 120 kA |
|---|--------|

**Voltage**

|                     |             |
|---------------------|-------------|
| Type voltage supply | AC          |
| Nominal voltage     | 500 - 500 V |

**Architecture**

|       |   |
|-------|---|
| Curve | C |
|-------|---|

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |