



L50603

**Fuse carrier 1P+N 32A 400V L38 1M**

**Technical Features**

**Dimensions**

Height	77 mm
Width	17.50 mm
Depth	75 mm

**Architecture**

Number of poles	2
Type of pole	1P+N

**Electric current**

Rated current	32 A
Rated current of fuse cartridge	2 A 4 A 6 A 8 A 10 A 12 A 16 A 20 A 25 A 32 A

**Capacity**

Number of modules	1
-------------------	---

**Use conditions**

Operating temperature	-5 - 40 °C
-----------------------	------------

**Installation, mounting**

Nominal tightening torque	1.80 - 1.80 Nm
Mounting on	DIN rail

**Power**

Total power loss under IN	1.50 W
---------------------------	--------

**Voltage**

Type voltage supply	AC
---------------------	----

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Connection**

Cross-section of input and output with screws, for flexible conductors	10 - 10 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	16 - 16 mm <sup>2</sup>

**Fuse**

Fuse size	10 x 38
-----------	---------

**Cover, door**

Interlockable	No
---------------	----

**Sustainability**

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

