



EPN410

**Electronic latching relay 1NO 230V**

**Technical Features**

**Electric current**

Rated current	16 A
Quiescent current	100 mA
Acceptable current rating AC1	16 A

**Capacity**

Number of modules	1
-------------------	---

**Connection**

Type of contacts	1NO
Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1 - 10 mm <sup>2</sup>
Number of contacts	1

**Voltage**

Command voltage AC	230 - 230 V
Command voltage DC	0 - 0 V
Command voltage 1	230 - 230 V
Rated operational voltage Ue	250 - 250 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Use conditions**

Operating temperature	-20 - 60 °C
Storage/transport temperature	-10 - 50 °C

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Power**

Total power loss under IN	1.20 W
Inrush power absorbed	5 VA

**Dimensions**

Height	85 mm
Width	18 mm
Depth	60 mm

**Lighting**

Max. load fluorescent lamp	280 VA
Max. load fluorescent lamp parallel compensated	300 VA

**Equipment**

Number of NO contacts	1
Number of NC contacts	0

**Sustainability**

RoHS conform	Yes
--------------	-----