



MU316A

**MCB 3P 6kA C-16A 3M**

**Technical Features**

**Electric current**

|                       |        |
|-----------------------|--------|
| Rated current         | 16 A   |
| Rated current -15°C   | 20.1 A |
| Rated current -10°C   | 19.7 A |
| Rated current -5°C    | 19.3 A |
| Rated current at 0°C  | 18.9 A |
| Rated current 5°C     | 18.4 A |
| Rated current 10°C    | 18 A   |
| Rated current 15°C    | 17.5 A |
| Rated current at 20°C | 17 A   |
| Rated current 25°C    | 16.5 A |
| Rated current 30°C    | 16 A   |
| Rated current 35°C    | 15.5 A |
| Rated current at 40°C | 14.9 A |
| Rated current at 45°C | 14.4 A |
| Rated current at 50°C | 13.8 A |
| Rated current 55°C    | 13.2 A |
| Rated current 60°C    | 12.5 A |
| Rated current 65°C    | 11.8 A |
| Rated current 70°C    | 11.1 A |

**Architecture**

|              |    |
|--------------|----|
| Type of pole | 3P |
| Curve        | C  |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

**Main electrical attributes**

|   |      |
|---|------|
| Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1 | 6 kA |
|---|------|

**Installation, mounting**

|   |                |
|---|----------------|
| Nominal tightening torque top terminal  | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.80 - 2.80 Nm |

**Voltage**

|  |             |
|--|-------------|
| Rated operational voltage U <sub>e</sub>         | 230 - 400 V |
| Type voltage supply                              | AC          |
| Rated insulation voltage U <sub>i</sub>          | 500 V       |
| Rated impulse withstand voltage U <sub>imp</sub> | 4000 V      |

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Connection**

|  |                        |
|--|------------------------|
| Cross-section of input and output with screws, for massive conductors  | 1 - 35 mm <sup>2</sup> |
| Cross-section of input and output with screws, for flexible conductors | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for flexible conductors            | 1 - 25 mm <sup>2</sup> |
| Cross-section of input with screws, for massive conductors             | 1 - 35 mm <sup>2</sup> |
| Cross-section flexible conductor                                       | 1 - 25 mm <sup>2</sup> |
| Cross-section rigid conductor  | 1 - 35 mm <sup>2</sup> |

**Installation, mounting**

|   |                |
|---|----------------|
| Nominal tightening torque                     | 2.80 - 2.80 Nm |
| Type of bottom connection for modular devices | biconnect      |
| Type of top connection for modular devices    | Screw terminal |
| 360° mounting position possible               | Yes            |

---

**Safety**

---

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

---

**Use conditions**

---

|  |                  |
|--|------------------|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2                |
| Class of energy limitation I <sup>2</sup> t              | 3                |
| Air humidity protection                                  | For all climates |
| Operating temperature                                    | -25 - 70 °C      |

---

**Power**

---

|                           |     |
|---------------------------|-----|
| Total power loss under IN | 7 W |
|---------------------------|-----|

---

**Connectivity**

---

|   |                  |
|---|------------------|
| Type of connection                            | Screw terminal   |
| Top connection alignment for modular devices  | Aligned terminal |
| Down connection alignment for modular devices | Aligned terminal |

---

**Dimensions**

---

|        |          |
|--------|----------|
| Height | 83 mm    |
| Width  | 52.50 mm |
| Depth  | 70 mm    |

---

**Sustainability**

---

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |

---