



TRB302B



**Module 2 inputs flush mounted 230V KNX QL**

**Technical Features**

**Architecture**

|            |                |
|------------|----------------|
| Bus system | Radio frequent |
|------------|----------------|

**Settings**

|                              |          |
|------------------------------|----------|
| Supported configuration mode | ETS easy |
|------------------------------|----------|

**Electric current**

|                          |   |
|--------------------------|---|
| Number of entry circuits | 2 |
|--------------------------|---|

**Equipment**

|                                   |    |
|-----------------------------------|----|
| External signal voltage necessary | No |
|-----------------------------------|----|

**Connectivity**

|                           |     |
|---------------------------|-----|
| With bus system KNX radio | Yes |
|---------------------------|-----|

**Equipment**

|                               |    |
|-------------------------------|----|
| Radio frequency bidirectional | No |
| With battery                  | No |
| With HVAC control             | No |

**Frequency**

|                        |               |
|------------------------|---------------|
| Frequency transmission | 868 - 868 MHz |
|------------------------|---------------|

**Installation, mounting**

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

**Lighting**

|                 |    |
|-----------------|----|
| LED controlling | No |
|-----------------|----|

**Materials**

|          |            |
|----------|------------|
| Material | Plastic    |
| Colour   | Light grey |
| RAL code | 7035       |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

**Cable**

|              |        |
|--------------|--------|
| Cable length | 0.20 m |
|--------------|--------|

**Voltage**

|                     |         |
|---------------------|---------|
| Input voltage       | 5 - 5 V |
| Type voltage supply | AC      |

**Texts**

|                    |   |
|--------------------|---|
| Installation mode  | For installation behind flush-mounted inserts |
| Type of connection | With screw-in lift terminals                  |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|