



TRE202



Module 2 outputs 10A IP55 KNX radio Quicklink

Technical Features

Connectivity

| | |
|----------------|-----------|
| Radio protocol | KNX Radio |
|----------------|-----------|

Settings

| | |
|------------------------------|-------------|
| Supported configuration mode | ETS easy |
|------------------------------|-------------|

Connectivity

| | |
|---------------------------|-----|
| Receiver category | 2 |
| With bus system KNX | No |
| With bus system KNX radio | Yes |

Dimensions

| | |
|----------------|------------|
| Dimensions | 35 x 85 mm |
| Height | 35 mm |
| Width | 85 mm |
| Built-in depth | 40 mm |

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

Equipment

| | |
|-------------------------------|-----|
| Radio frequency bidirectional | Yes |
| With switch for manual switch | No |

Electric current

| | |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

Frequency

| | |
|---------------------------|---------------------|
| Frequency | 50 - 50 Hz |
| Radio reception frequency | 868.30 - 868.30 MHz |

Power

| | |
|-------------------------------------|--------|
| Output power | 2300 W |
| 230 V incandescent and halogen lamp | 1500 W |

Voltage

| | |
|----------------------------|-------------|
| Operating voltage | 230 - 230 V |
| System supply voltage | 230 V AC |
| Operating voltage over bus | 21 - 32 V |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP55 |
|-------------------------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10 - 55 °C |
|-----------------------|-------------|

Texts

| | |
|--------------------|---|
| Function | Easy additional functions: +6 scenes Repeat function can be activated to increase the radio range Reset function (to factory setting) |
| Type of connection | With screw-in lift terminals |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|