



WNC001B

**Cubyko LT 2-way switch wall mounted white IP55**

**Technical Features**

**Electric current**

Switching current	10 A
-------------------	------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Voltage**

Rated voltage	250 V
---------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Satin finish
Material	Thermoplastic
Treatment	Untreated

**Identification**

Assembly arrangement	Basic element with complete housing
----------------------	-------------------------------------

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Dimensions	76 x 76 mm
Built-in depth	0 mm
Built-in depth flush-mounted boxes	40 mm

**Safety**

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

**Architecture**

Control/operation element	Single rocker
---------------------------	---------------

**Electric current**

Rated current	10 A
---------------	------

**Texts**

Installation mode	For screw fastening
Type of connection	With plug-in terminals
Switch mode	Change-over

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes