



HNA126Z

Moulded Case Circuit Breaker h3 x160 TM FIX 4P4D 125A 40kA CTC

Technical Features

Electric current

Rated current	125 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	85 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	40 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	20 kA
Rated current 10°C according to IEC 60947	148,80 A
Rated current 15°C according to IEC 60947	146 A
Rated current 20°C according to IEC 60947	143,20 A
Rated current 25°C according to IEC 60947	140,30 A
Rated current 30°C according to IEC 60947	137,40 A
Rated current at 35°C according to IEC 60947	134,40 A
Rated current at 40°C according to IEC 60947	131,30 A
Rated current 45°C according to IEC 60947	128,20 A
Rated current 50°C according to IEC 60947	125 A
Rated current 55°C according to IEC 60947	121,60 A
Rated current at 60°C according to IEC 60947	118,20 A
Rated current 65°C according to IEC 60947	114,70 A
Rated current 70°C according to IEC 60947	111,10 A

Architecture

Number of poles	4
-----------------	---

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	690 V

Functions

Trip unit	TM F/F
-----------	--------

Power

Total power loss under IN	33 W
---------------------------	------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	4 - 70 mm ²
Cross-section rigid conductor	4 - 95 mm ²

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Settings

Thermal protection knob setting xIN	1
	1

Product Datasheet

HNA126Z

Dimensions		
Height		130 mm
Width		100 mm
Depth		68 mm
Compatibility		
Suitable for DIN Rail		No
Main electrical attributes		
Magnetic protection trip time		0 - 0 ms
Sustainability		
REACH-SVHC free		Yes
RoHS conform		Yes