



WNA045

IP55

Cubyko LT 2-gang 2-way push-button 10/1F composable with light grey IP55

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Double push button
---------------------------	--------------------

Materials

Colour	Grey
Surface finish	Satin finish
Material	Thermoplastic
Treatment	Untreated
Transparent	No
Backside internal	Matt

Dimensions

Height	75 mm
Width	75 mm
Depth	40 mm
Built-in depth flush-mounted boxes	40 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Indicator lamp	As an accessory
Number of buttons	2
Type of push button	Single push button
With feedback signal contact	No

Connectivity

Type of connection	quickconnect
--------------------	--------------

Connection

Connector/plug type	Turn screw lock
---------------------	-----------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	For screw fastening
Switch mode	Change-over
Type of connection	With plug-in terminals

Suitable for

cubyko	
--------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes
