



WMSS82-USBAC

### Double Pole Switched Socket 2 Gang Complete With Twin USB A+C Ports

#### Technical Features

##### Electric current

Rated current	13 A
---------------	------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

##### Dimensions

Height	86 mm
Width	146 mm
Depth	19 mm
Built-in depth flush-mounted boxes	25 mm

##### Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

##### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting
Connector/plug type USB	AC

##### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	0
-------------------	---

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Functions

With orientation lighting	No
With function lighting	No

##### Texts

Imprint	With imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes