



L502PV

Fuse carrier 2P 1000V DC L38 2M

Technical Features

Architecture

Number of poles	2
Type of pole	2P

Capacity

Number of modules	2
-------------------	---

Electric current

Rated current	32 A
Rated conditional short-circuit current I _{cc} with gI-gG fuses	30 kA
Rated short-time withstand current I _{ow} IEC 60947	30 kA

Voltage

Rated operational voltage U _e	690 - 1000 V
Type voltage supply	DC
Rated insulation voltage U _i	690 V
Nominal voltage	0 - 1000 V

Electric current

Rated ultimate short-circuit breaking capacity I _{cu} AC IEC 60947-2	30 kA
-------------------------------------------------------------------------------	-------

Voltage

Rated operational voltage in DC	0 - 1000 V
---------------------------------	------------

Installation, mounting

Nominal tightening torque	2 - 2 Nm
---------------------------	----------

Dimensions

Height	77 mm
Width	35 mm
Depth	75 mm

Power

Total power loss under I _N	2.20 W
---------------------------------------	--------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-25 - 50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3

Connection

Cross-section flexible conductor	0.75 - 10 mm ²
Cross-section rigid conductor	1 - 16 mm ²

Frequency

Frequency	50 - 60 Hz
-----------	------------

Sustainability

RoHS conform	Yes
--------------	-----