



SPN140D

SPD 1P pluggable 40kA class 2 with end of life indicator

Technical Features

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U_e	240 - 415 V
Continuous operating voltage U_c according to IEC 61643-1	275 V
Voltage protection level U_p according to IEC 61643-1	1.20 kV
Voltage protection level U_p L-PE/N-PE according to IEC 61643-11	1 kV

Electric current

Nominal discharge current I_n 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	15 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge (I_{max}) L-N(PEN)/ N-PE	40 kA

Dimensions

Height	96.8 mm
Width	17.6 mm
Depth	58.2 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN-C
--------------	------

Equipment

With remote signalling contact	No
--------------------------------	----

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3.60 - 3.60 Nm
---------------------------	----------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes