



SPA932

SPD T1+T2 4P TN-S TT 50kA Up 1,2kV

Technical Features

Electric current

Max. discharge (Imax) L-N(PEN)/ N-PE	50 kA
--------------------------------------	-------

Network configuration

Network type	TN-S TT
--------------	------------

Electric current

Max. overcurrent protection device, parallel connection (fuse)	160 A
--	-------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Electric current

Lightning impulse current Iimp (10/350 μs) IEC 61643 L-N(PEN)/ N-PE	12.5 kA 50 kA
---	------------------

Equipment

With remote signalling contact	No
--------------------------------	----

Capacity

Number of modules	4
-------------------	---

Voltage

Voltage protection level Up according to IEC 61643-1	1.20 kV
Continuous operating voltage Uc according to IEC 61643-1	335 V
Rated operational voltage Ue	240 - 415 V
Voltage level Up L-N/PEN IEC 61643-11	1.2 kV

Architecture

Number of poles	4
-----------------	---

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Dimensions

Height	89.80 mm
Width	71.20 mm
Depth	77.50 mm

Controls and indicators

With indicator lamp	Yes
---------------------	-----

Standards

Requirement class IEC 61643	T1 T2
-----------------------------	----------

Installation, mounting

Nominal tightening torque	3 - 4.5 Nm
Mounting on	DIN rail

Connection

Cross-section of input and output with screws, for flexible conductors	1.5 - 25.0 mm ²
Cross-section of input and output with screws, for massive conductors	1.5 - 35.0 mm ²
Cross-section signal contact	0.4 - 1.5 mm ²

Frequency

Frequency	50 - 60 Hz
-----------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Configuration

With integrated protection fuse	No
---------------------------------	----

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----
