



VB418B

Small distributor,vega,surface,4row,72M,IP40,QC-terminal,PE,white door

**Technical Features**

**Installation, mounting**

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

**Equipment**

|                            |    |
|----------------------------|----|
| Number of rails            | 4  |
| Number of rows             | 4  |
| With lock                  | No |
| Has neutral terminal block | No |

**Capacity**

|                   |    |
|-------------------|----|
| Number of modules | 72 |
|-------------------|----|

**Dimensions**

|        |        |
|--------|--------|
| Height | 775 mm |
| Width  | 400 mm |
| Depth  | 146 mm |

**Cover, door**

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
| Number of locks         | 1 |

**Dimensions**

|                       |    |
|-----------------------|----|
| Number of width units | 18 |
|-----------------------|----|

**Cover, door**

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

**Materials**

|          |                  |
|----------|------------------|
| Material | Polystyrene (PS) |
| RAL code | 9010             |
| Colour   | White            |

**Equipment**

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate          | No  |

**Safety**

|                               |                              |
|-------------------------------|------------------------------|
| Protection class              | Isolation class II           |
| Impact resistance IK          | IK07                         |
| Ingress Protection (IP) class | IP40                         |
| Locking type                  | Snap on lock<br>Without lock |
| Glow wire test                | 650 °C                       |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|