



P64AXILSF1.0

### P64AX c/w 4 Core 0.75mm<sup>2</sup> 1m LSOH Lead

#### Technical Features

##### Architecture

|                 |   |
|-----------------|---|
| Number of poles | 4 |
|-----------------|---|

##### Voltage

|                        |       |
|------------------------|-------|
| Max. operating voltage | 240 V |
|------------------------|-------|

##### Electric current

|               |     |
|---------------|-----|
| Rated current | 6 A |
|---------------|-----|

##### Cable

|              |     |
|--------------|-----|
| Cable length | 1 m |
|--------------|-----|

##### Dimensions

|        |         |
|--------|---------|
| Length | 1000 mm |
|--------|---------|

##### Connection

|                         |                             |
|-------------------------|-----------------------------|
| Conductor cross-section | 0.75 - 0.75 mm <sup>2</sup> |
|-------------------------|-----------------------------|

##### Equipment

|                   |                         |
|-------------------|-------------------------|
| Mechanical coding | Yes                     |
| Type cable side 1 | Plug                    |
| Type cable side 2 | Free conductor end      |
| Type of cable     | Device connection cable |

##### Use conditions

|                                                          |   |
|----------------------------------------------------------|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
|----------------------------------------------------------|---|

##### Materials

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

##### Cable

|                                          |       |
|------------------------------------------|-------|
| Cable permanent temperature resistant to | 90 °C |
|------------------------------------------|-------|

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |