




EHN171



Weekly time switch 1 channel, 3 modules with reserve

Technical Features

Equipment

| | |
|--------------------|---|
| Number of channels | 1 |
|--------------------|---|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Power

| | |
|-------------------------------------|-------------|
| Power consumption during operation | 0.50 W |
| 230 V incandescent and halogen lamp | 1100 W |
| Power incandescent lamp | 900 - 900 W |

Functions

| | |
|-----------------------------|---|
| Number of function channels | 1 |
|-----------------------------|---|

Connection

| | |
|----------------------------------|-------------------------|
| Number of contacts | 1 |
| Cross-section flexible conductor | 0.5 - 6 mm ² |
| Cross-section rigid conductor | 0.5 - 6 mm ² |

Use conditions

| | |
|-----------------------|--------------|
| Operating temperature | -10 - +55 °C |
|-----------------------|--------------|

Capacity

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Dimensions

| | |
|--------|-------|
| Height | 90 mm |
| Width | 54 mm |
| Depth | 60 mm |

Texts

| | |
|-------------------|--------------------------|
| Switch mode | Change-over contact |
| Installation mode | For mounting on DIN rail |

Electric current

| | |
|--------------------------|-----|
| Max. power (cos phi 0,6) | 4 A |
|--------------------------|-----|

Endurance

| | |
|--|-------|
| Electrical durability at nominal load in AC1 in operating cycles | 50000 |
|--|-------|

Texts

| | |
|--------------------|----------------------|
| Type of connection | With screw terminals |
|--------------------|----------------------|

Voltage

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 230 - 240 V |
|------------------------------|-------------|

Power

| | |
|-------------------------|-----|
| Power loss at full load | 1 W |
|-------------------------|-----|

Settings

| | |
|-------------------------|------------------------------|
| Programme cycles | Programme cycles: 1 x 7 days |
| Shortest switching time | 2 h |

Lighting

| | |
|----------------|-------|
| LED lamp power | 180 W |
|----------------|-------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |