



LS503

**Fuse 3P 32A 690V L38 3M**

**Technical Features**

**Dimensions**

Height	83 mm
Width	54 mm
Depth	75 mm

**Architecture**

Number of poles	3
Type of pole	3P

**Electric current**

Rated current	32 A
---------------	------

**Capacity**

Number of modules	3
-------------------	---

**Use conditions**

Operating temperature	-5 - 50 °C
-----------------------	------------

**Installation, mounting**

Nominal tightening torque	2.20 - 2.20 Nm
Mounting on	DIN rail

**Power**

Total power loss under IN	11.10 W
---------------------------	---------

**Voltage**

Rated insulation voltage $U_i$	690 V
Type voltage supply	AC

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Connection**

Cross-section of input and output with screws, for flexible conductors	0.75 - 16 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	1 - 25 mm <sup>2</sup>

**Fuse**

Fuse size	10 x 38
-----------	---------

**Cover, door**

Interlockable	Yes
---------------	-----

Illustrations | Drawings

