



ECP310D

**3 Phase kWhmeter direct 125A 6M S0 MID**

**Technical Features**

**Architecture**

Type of pole	3P+N
--------------	------

**Electric current**

Rated current	125 A
---------------	-------

**Capacity**

Number of modules	6
-------------------	---

**Connectivity**

Type of connection	Direct connection
--------------------	-------------------

**Dimensions**

Height	92 mm
Width	107 mm
Depth	60 mm

**Equipment**

Type of pulse generator	Electrical
-------------------------	------------

**Compatibility**

Suitable for	Purchase/supply
--------------	-----------------

**Connection**

Cross-section of metering input	50 - 50 mm <sup>2</sup>
Cross-section of metering output	50 - 50 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	5 - 5 Nm
Mounting on	DIN rail

**Mechanical features**

Nominal tightening torque digital terminal	0.50 - 0.50 Nm
--	----------------

**Measurement**

Measuring system	Direct measurement
Type of measuring instrument	Electronic
Current measurement range	0.25 - 125.0 A
Measurement range voltage Ph-N	92 - 276 V
Measurement range voltage Ph-Ph	160 - 480 V
Frequency measuring range	45 - 65 Hz

**Functions**

Accuracy class	B
Tariff type	T1...T2 (230 V AC)/-
Is calibrated	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-25 - 55 °C
Storage/transport temperature	-25 - 70 °C

**Power**

Power consumption VA	2 VA
Total power loss under IN	0.60 W

**Electric current**

Maximum measuring circuit current	125 A
-----------------------------------	-------

---

**Frequency**

---

Frequency	50 - 50 Hz
-----------	------------

---

**Sustainability**

---

REACH-SVHC free	Yes
-----------------	-----

---

RoHS conform	Yes
--------------	-----

---