




TXA663A



DIMMER 3 CHANNELS 300W NE

Technical Features

Voltage

Operating voltage over bus	21 - 32 V
Input voltage	230 - 230 V
System supply voltage	30 V DC Via bus
Auxiliary tension	230 - 230 V

Electric current

Bus current consumption data transfer	2.30 mA
---------------------------------------	---------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connection

Cross-section flexible conductor	0.25 - 0.75 mm ²
Cross-section rigid conductor	0.75 - 2.5 mm ²

Equipment

Number of outputs	3
-------------------	---

Lighting

LED lamp power	210 W
----------------	-------

Equipment

Type of dimmer	Dimming actuator
----------------	------------------

Capacity

Number of modules	6
-------------------	---

Power

230 V incandescent and halogen lamp	300 W
Power incandescent lamp	900 - 900 W
Power of variator	900 - 900 W

Connectivity

With bus system KNX radio	No
Type of connection	quickconnect

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Texts

Fuse	Overheating protection (display using LEDs) Short-circuit and overload-proof (electronic fuse) Short-circuit proof and overload-proof (display using LEDs)
Dimming principle	Phase cut-on or cut-off according to load type, self-learning Minimum/maximum dimming values per channel settable on device
Function	Learning function for optimised operation of compact fluorescent lamps and LED luminaires can be activated via the bus
Type of connection	With quickconnect plug-in terminals
Labelling	Large labelling field
Protection	With overheating, overload and short-circuit protection

Sustainability

RoHS conform	Yes
--------------	-----