




EE815



**Presence detector 360° monobloc, flush mounted, white**

**Technical Features**

**Detection**

Detection angle	360 - 360
Type of sensor	Presence detector

**Settings**

Time delay	1 Min - 1 h
------------	-------------

**Lighting**

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Dimensions**

Width	80 mm
Built-in depth	70 mm
Recommended installation height	2.5 - 3.5 m

**Use conditions**

Operating temperature	-10 - 45 °C
-----------------------	-------------

**Materials**

Colour	White
Material	Plastic

**Safety**

Ingress Protection (IP) class	IP41
-------------------------------	------

**Installation, mounting**

Mounting on	Flush mounting
Suitable for outdoor usage	Yes

**Texts**

Function	Can only be used as individual unit
Installation mode	With spring clips for ceiling installation
Type of connection	With screw terminals

**Sustainability**

RoHS conform	Yes
--------------	-----