



CDA690

RCCB 3P+N 125A 30mA A

Technical Features

Architecture

Type of pole	3P+N
Number of poles	4

Electric current

Rated current I_N	125 A
Rated residual operating current I_{dn}	30 mA
Breaking and opening capacity I_{dm}	1.25 kA
Rated conditional short-circuit current I_{nc} according to EN61008-1	10 kA
Rated current at -25°C	125 A
Rated current at -20°C	125 A
Rated current at -15°C	125 A
Rated current at -10°C	125 A
Rated current at -5°C	125 A
Rated current at 0°C	125 A
Rated current at 5°C	125 A
Rated current at 10°C	125 A
Rated current at 15°C	125 A
Rated current at 20°C	125 A
Rated current at 25°C	125 A
Rated current at 30°C	125 A
Rated current at 35°C	125 A
Rated current at 40°C	125 A
Rated current at 45°C	120 A
Rated current at 50°C	115 A
Rated current at 55°C	110 A
Rated current at 60°C	100 A
Rated current at 65°C	95 A
Rated current at 70°C	90 A

Installation, mounting

Nominal tightening torque top terminal	3.60 - 3.60 Nm
Nominal tightening torque down terminal	3.60 - 3.60 Nm

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Voltage

Rated operational voltage U_e	240 - 415 V
Type voltage supply	AC
Rated insulation voltage U_i	500 V
Dielectric strength value of power frequency	2 kV
Rated impulse withstand voltage U_{imp}	4000 V
Rated impulse withstand voltage U_{imp} IEC 60947-3	6000 V
Max. operating voltage	456 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Capacity

Number of modules	4
-------------------	---

Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----

Safety

Residual current type	A
Ingress Protection (IP) class	IP20

Installation, mounting

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

Connection

Cross-section of output with screws, for massive conductors	1 - 50 mm ²
Cross-section of output with screws, for flexible conductors	1 - 35 mm ²
Cross-section of input and output with screws, for flexible conductors	1 - 35 mm ²
Cross-section of input and output with screws, for massive conductors	1 - 50 mm ²

Power

Power dissipation at IN	29.20 W
-------------------------	---------

Use conditions

Max. altitude	2000 m
Operating temperature	-25 - 40 °C

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Connectivity

Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

Dimensions

Height	85 mm
Width	72 mm
Depth	70 mm

Sustainability

RoHS conform	Yes
--------------	-----