



CFC625J

**RCCB 3P+N 25A 300mA AC**

**Technical Features**

**Architecture**

Type of pole	3P+N
--------------	------

**Electric current**

Rated current	25 A
Rated residual operating current Idn	300 mA
Breaking and opening capacity Idm	1.25 kA
Rated conditional short-circuit current I <sub>nc</sub> according to EN61008-1	10 kA
Rated current -25°C	25 A
Rated current at -20°C	25 A
Rated current -15°C	25 A
Rated current -10°C	25 A
Rated current -5°C	25 A
Rated current at 0°C	25 A
Rated current 5°C	25 A
Rated current 10°C	25 A
Rated current 15°C	25 A
Rated current at 20°C	25 A
Rated current 25°C	25 A
Rated current 30°C	25 A
Rated current 35°C	25 A
Rated current at 40°C	25 A
Rated current at 45°C	25 A
Rated current at 50°C	25 A
Rated current 55°C	25 A
Rated current 60°C	25 A
Rated current 65°C	25 A
Rated current 70°C	25 A

**Installation, mounting**

Nominal tightening torque top terminal	3.60 - 3.60 Nm
Nominal tightening torque down terminal	3.60 - 3.60 Nm

**Voltage**

Rated operational voltage Ue	230 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Dielectric strength value of power frequency	2 kV
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Rated impulse withstand voltage U <sub>imp</sub> IEC 60947-3	6000 V
Max. operating voltage	440 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Capacity**

Number of modules	4
-------------------	---

**Compatibility**

Suitable for DIN Rail	Yes
-----------------------	-----

**Safety**

Residual current type	AC
Ingress Protection (IP) class	IP20

**Installation, mounting**

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

<b>Connection</b>	
Cross-section of output with screws, for massive conductors	1 - 25 mm <sup>2</sup>
Cross-section of output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
<b>Power</b>	
Total power loss under IN	1.98 W
<b>Use conditions</b>	
Max. Altitude	2000 m
<b>Endurance</b>	
Electric endurance in number of cycles	10000
Number of mechanical operations	20000
<b>Connectivity</b>	
Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
<b>Dimensions</b>	
Height	85 mm
Width	72 mm
Depth	70 mm
<b>Sustainability</b>	
RoHS conform	Yes