



MMN204

Magnetic MCB 2P 25kA 4A 400V Zubehörmöglich. Anzeige IEC 947-2

#### Technical Features

##### Electric current

Rated current	4 A
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	20 kA
Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	25 kA

##### Architecture

Type of pole	2P
Curve	Mag

##### Capacity

Number of modules	2
-------------------	---

##### Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

##### Voltage

Rated operational voltage Ue	415 - 415 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6000 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>

##### Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

##### Power

Total power loss under IN	0.40 W
---------------------------	--------

##### Endurance

Electric endurance in number of cycles	4000
--	------

##### Connectivity

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

# Product Datasheet

## MMN204

---

### Dimensions

Height	83 mm
Width	35 mm
Depth	70 mm

### Sustainability

RoHS conform	Yes
--------------	-----

### Illustrations | Drawings

