



SPB015D

Cartridge L-N Uc 275V In 5kA I_{max} 15kA Up 1kV

Technical Features

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U _e	240 - 415 V
Continuous operating voltage U _c according to IEC 61643-1	275 V
Voltage protection level U _p according to IEC 61643-1	1.35 kV
Voltage level U _p L-N/PEN IEC 61643-11	1.35 kV
Type voltage supply	AC

Electric current

Nominal discharge current I _n 8 - 20 μs L-N(PEN)/N-PE IEC 61643	5 kA
--	------

Dimensions

Height	52.4 mm
Width	17.5 mm
Depth	55.3 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN TT
--------------	----------

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3 - 3 Nm
---------------------------	----------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes