



LS612

**Fuse carrier 1P+N 50A 690V L51 accessoriability 3M**

**Technical Features**

**Dimensions**

Height	107 mm
Width	52.50 mm
Depth	93 mm

**Architecture**

Number of poles	2
Type of pole	1P+N

**Electric current**

Rated current	50 A
Rated current of fuse cartridge	2 A 4 A 6 A 10 A 12 A 16 A 20 A 25 A 32 A 40 A 50 A

**Capacity**

Number of modules	3
-------------------	---

**Use conditions**

Operating temperature	-5 - 40 °C
-----------------------	------------

**Installation, mounting**

Nominal tightening torque	3.5 - 3.5 Nm
Mounting on	DIN rail

**Power**

Total power loss under IN	8.30 W
---------------------------	--------

**Voltage**

Rated insulation voltage $U_i$	690 V
Rated impulse withstand voltage $U_{imp}$	8 kV
Type voltage supply	AC
Overvoltage category according to IEC 60947-1	3

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Connection**

Cross-section of input and output with screws, for flexible conductors	16 - 16 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	25 - 25 mm <sup>2</sup>

**Fuse**

Fuse size	14 x 51
-----------	---------

**Cover, door**

Interlockable	Yes
---------------	-----

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

