



L12601

Fuse carrier 1P+N 20A 400V 1M

Technical Features

Dimensions

Height	77 mm
Width	17.50 mm
Depth	75 mm

Architecture

Number of poles	1
-----------------	---

Electric current

Rated current	20 A
Rated current of fuse cartridge	0.5 A 1 A 2 A 4 A 6 A 8 A 10 A 12 A 16 A 20 A

Capacity

Number of modules	1
-------------------	---

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Installation, mounting

Nominal tightening torque	1.80 - 1.80 Nm
Mounting on	DIN rail

Power

Total power loss under IN	1.50 W
---------------------------	--------

Voltage

Type voltage supply	AC
---------------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Cross-section of input and output with screws, for flexible conductors	10 - 10 mm ²
Cross-section of input and output with screws, for massive conductors	16 - 16 mm ²

Fuse

Fuse size	8.5 x 31.5
-----------	------------

Cover, door

Interlockable	No
---------------	----

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

