



SPB420

SPD 4P T2 TNS/TT Uc 350V In 20kA Imax 40kA 315A

Technical Features

Capacity

Number of modules	2.70
-------------------	------

Voltage

Rated operational voltage Ue	240 - 415 V
Continuous operating voltage Uc according to IEC 61643-1	275 V
Voltage protection level Up according to IEC 61643-1	1.50 kV
Voltage protection level Up L-PE/N-PE according to IEC 61643-11	1.50 kV
Voltage level Up L-N/PEN IEC 61643-11	1500 V

Electric current

Nominal discharge current In 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	20 kA
Max. discharge (Imax) L-N(PEN)/ N-PE	40 kA

Dimensions

Height	89.9 mm
Width	49.20 mm
Depth	71.2 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN-S TT
--------------	------------

Equipment

With remote signalling contact	No
--------------------------------	----

Connection

Cross-section of input and output with screws, for flexible conductors	1.5 - 25.0 mm ²
Cross-section of input and output with screws, for massive conductors	1.5 - 35.0 mm ²

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	4.5 - 4.5 Nm
---------------------------	--------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes